

Morse

suspension lamp



Table of contents

1. Product overview	Page 2
2. Finishes and materials	Page 2
3. Light Source & dimming	Page 2
4. Functionality & accessories	Page 3
5. Installation	Page 3
6. Recommended use & installation height	Page 4
7. Photometric data and technical information	Page 4
8. Ordering codes	Page 5
9. Certifications & standards	Page 6
10. Maintenance & Cleaning	Page 6

Versions



MOR_3915
Page 4

Morse

suspension lamp

1. Product overview

Metallic suspension lamp with integrated LED, providing direct lighting. Equipped with three independent heads, each rotatable up to 320°, allowing precise light direction towards the table, wall, or ceiling. Height adjustable.

Multiple Morse units can be mechanically linked using a connector piece (Union Kit) to extend the installation length. Each unit requires its own ceiling-mounted electrical connection.



2. Finishes and Materials



Body: 26 Black (RAL 9005)
94 Champagne (RAL 1035)

Surface Canopy: 26 Black
94 Champagne



Recessed Canopy: 26 Black
74 White

3. Light Source & Dimming

Lamping per head (x3)

LED 6,2W

(Ang. 85° embedded nylon lens / >90 CRI / 350mA)

230V / Typ* 725 lumens

*Integrated LED module (included)

*Alternative 60°exposed acrylic lens (included)

Dimming options:

Standard: TRIAC (included)

Optional: DALI, CASAMBI

Optional optic: embedded aluminium optic 20°

Morse

suspension lamp

4. Functionality & Accessories

Three possible optic lenses

Standard configuration includes a 85° recessed nylon optic designed to improve visual comfort and reduce glare. It provides soft, uniform illumination with minimal visual impact.

A 60° methacrylate optic is supplied in the box, allowing the user to choose the preferred lighting effect. This option creates a subtle, decorative line of light visible from the side.

Optional architectural optic conceals the LED source within a 20° conical aluminium lens. It projects light exclusively downward (no lateral emission), offering precise control.



Nylon optic
85° beam angle
*included & installed

Methacrylate optic
60° beam angle
*included, not installed

Aluminium optic
20° beam angle
*not included, accessory


Rotating heads

Three independent lighting heads, each rotating up to 320°, provide precise light direction and can be adjusted individually to create different lighting scenarios, from focused task lighting to ambient illumination.



Possible compositions

Optional **Union Kit Accessory** for connecting multiple fixtures, enabling expanded and customized lighting configurations. Each unit requires its own ceiling-mounted electrical connection. To order the accessory, please specify code 123915XX2



5. Installation

Surface canopy



Recessed canopy with remote driver



Ø 55 mm drill on
dropped ceiling

Morse

suspension lamp


6. Recommended use & Installation height

Suitable for general lighting, as well as for direct illumination above dining tables, countertops, bars, or desks. We **recommend positioning** the light source approximately **85 cm above the surface**. For more accurate information, refer to the photometric report.

7. Photometric Data and Technical Information


Photometric data corresponds to each individual lamp. 2D, 3D, and BIM files also available in the download area. Access to all technical files directly here.

Nylon optic 85°




H[m]	D[m]	Max lux	Med lux	Alpha=42.5°+42.5°	G=0.0 Máx no a G
1.00	1.84	302	128		
2.00	3.67	75	32		
3.00	5.51	34	14		
4.00	7.34	19	8		
5.00	9.18	12	5		

Methacrylate optic 60°



H[m]	D[m]	Max lux	Med lux	Alpha=28.8°+28.8°	G=0.0
1.00	1.10	430	230		
2.00	2.20	108	57		
3.00	3.30	48	26		
4.00	4.41	27	14		
5.00	5.51	17	9		

Aluminium optic 20°



H[m]	D[m]	Max lux	Med lux	Alpha=10.1°+10.1°	G=0.0
1.00	0.36	2047	1259		
2.00	0.71	512	315		
3.00	1.07	227	140		
4.00	1.43	128	79		
5.00	1.79	82	50		

Morse

suspension lamp

8. Ordering Codes

Lamping

LED 6,2W

(Ang. 85° embedded nylon lens / >90 CRI / 350mA)

230V / Typ* 725 lumens

*Integrated LED module (included)

*Alternative 60°exposed acrylic lens (included)

Dimming options: TRIAC (Optional: DALI, CASAMBI)

Finishes

Body & Surface Canopy:

26 Black

94 Champagne

Recessed Canopy:

26 Black

74 White



Drawing	Mounting	Finish Canopy	Finish Body	Ordering Code
MOR_3915S 	Surface mounted. Driver in the canopy.	Black	Black	MOR_3915S_2626W
		Champagne	Champagne	MOR_3915S_9494W
MOR_3915R 	Recessed, Remote driver Ø 50 mm drill	Black	Black	MOR_3915R_2626W
		White	Black	MOR_3915R_7426W
		Black	Champagne	MOR_3915R_2694W
		White	Champagne	MOR_3915R_7494W

Lens Ordering Codes:

One 20° embedded lens per head


Black 3 units of 123530263

Champagne 3 units of 123530943

Morse

suspension lamp

9. Certifications & Standards



Warranty: 2 years

100% made in Spain

10. Maintenance & Cleaning

Our lighting fixtures are crafted with high-quality materials and finishes to ensure durability and timeless elegance. To maintain their original beauty, please follow these care recommendations:

1. Regular cleaning: Dust the fixture regularly using a soft, dry microfiber cloth to prevent buildup.
2. For deeper cleaning: If necessary, use a slightly damp cloth with clean water. Always dry the surface immediately with a dry cloth.
3. Avoid harsh products: Do not use alcohol, abrasive cleaners, solvents, or detergents, as they may damage the finish and alter the appearance.

In case of failure, LEDs can be easily replaced.